

Haag-Streit Contact Glasses: Diagnostic and Laser.

Superb Haag-Streit optics.
Total quality control.
Special bonding technique.

For slit lamps with shorter distance-to-reduction prisms
630/630 S – 3-mirror design, also available as 630L Laser Contact Glass.



630

630 L

The Classic Goldmann Glass
903/903 S – 3-mirror design, also available as 903L Laser Contact Glass.



903

903 L

Contact Glass for Newborns 906 – 10 mm internal diameter, 3 mirror design. Also available as 906L Laser Contact Glass.



906

Contact Glass for Children up to age 4 907 – 11 mm internal diameter, 3 mirror design, also available as 907L Laser Contact Glass.



907

Fundus Glass
901 – For binocular observation of pupil, macula and vitreous body sections



901

Ora Serrata Glass
(one-mirror design)
904 – View the ora serrata, the paras plana and the extreme peripheral parts of vitreous body and ocular fundus



904

Glaucoma Glasses
902/902 S – One-mirror Glaucoma glass



902

902 S

905/905S – Two-mirror contact glass for the iridocorneal angle



905

905 S

Laser Contact Glasses

CGAL
for laser treatments of the chamber angle.



CGI
for full-thickness peripheral laser iridectomies



CGI 1

CGRL
for photocoagulation and diagnosis of the retina



CGRL

CGV
for YAG laser procedures in the posterior vitreous.



CGV 1